

Set

MMS 2040



4 mm safety system

Product	MMS 2040
description	Test equipment set for safety applications, as accessories for measuring instruments. - KLEPS 2600 Safety clamp-type test probe with rotating grip jaws and flexible shaft for clamping of pins and wires up to $\varnothing$ 4 mm. - AK 2 B Contact-protected alligator clip for clamping of finest wires, clamping range up to a maximum of 9.5 mm bolt diameter. - PL 2600 S Safety measuring lead with dual function safety test probe for penetration of and oxide layers and safety connector with straight outlet. (length: 100 cm) - MLS WG 100/1 Safety measuring lead with 4 mm plugs on both sides, one straight and one angled outlet. (length: 100 cm) Please find further technical details on individual product data sheets.
Articlenumber	972342001
technical data	
scope of delivery	1 x clamp-type test probe KLEPS 2600 black (972 306-100) 1 x clamp-type test probe KLEPS 2600 red (972 306-101) 1 x alligator clip AK 2 B black (932 435-100) 1 x alligator clip AK 2 B red (932 435-101) 1 x test lead PL 2600 S black (934 159-100) 1 x test lead PL 2600 S red (934 159-101) 1 x measuring lead MLS WG 100/1 black (934 082-100) 1 x measuring lead MLS WG 100/1 red (934 082-101)

stand : November 13, 2025 5:59 PM