



Clamp-type test probe

KLEPS 2600



Product	KLEPS 2600
description	Safety clamp-type test probe with rotating grip jaws and flexible shaft. Wires and pins with up to a maximum diameter of 4mm can be clamped thanks to the special form of the grip jaws. 4mm diameter brass socket connection.
operating instruction	BA457
article-no. / *colour	● 00 black ● 01 red
drawing	
	
technical data	
connection	unsprung socket 4 mm
rated voltage	AC/DC 1000 V
measurement cat. acc. to IEC 61010	CAT II
rated current (consider derating curve)	4 A
material plug	spring steel
material socket	brass
housing material	PBT
temperature range acc. To IEC61010 ⁽¹⁾	-25 °C to +70 °C
flammability class acc. to UL 94 (only valid for basic material of housing)	HB
clamp type	rotating grip jaws, tin plated

4 mm safety system

clamping range	4 mm
----------------	------

⁽¹⁾contact the manufacturer for applications at deviating temperature ranges

stand : November 13, 2025 5:59 PM