


Measuring leads

MVLF WS 2/10



Product	MVLF WS 2/10
description	Injection-moulded measuring lead at either end 2 mm spring-loaded pin and 2 mm diameter unsprung socket for tower constructions. Highly flexible stranded lead, grip and lead shatter-proof.
operating instruction	BA201
article-no. / *colour	9381101xx  00 black  01 red
drawing	
	 Buchse für 2 mm Stecker socket for 2 mm plug
technical data	
rated voltage	30 VAC / 60 VDC
measurement cat. acc. to IEC 61010	O ⁽²⁾
rated current (consider derating curve)	6 A
material plug	brass, nickel plated
housing material	PP
temperature range acc. To IEC61010 ⁽¹⁾	-15 °C to +60 °C
flammability class acc. to UL 94 (only valid for basic material of housing)	HB
cable length	10 cm
conductor size	0,5 mm ²

⁽¹⁾contact the manufacturer for applications at deviating temperature ranges

⁽²⁾without rated measurement category, for other circuits that are not directly connected to mains

stand : November 13, 2025 5:59 PM