



The DNA of tech.™

Product Termination Notification

Product Group: CC/Thursday May 21, 2026/PTN-CC-00004-2026-REV-0



Obsolescence of some T&R items from CeraMite brand

For further information, please contact your regional Vishay office.

CONTACT INFORMATION

Americas

Florian Weyland
Dr.-Felix-Zandman-Platz 1
-
Selb Germany 95100
Phone: +49-9287-71-2787
Fax:
-

Europe

Florian Weyland
Dr.-Felix-Zandman-Platz 1
-
Selb Germany 95100
Phone: +49-9287-71-2787
Fax:
-

Asia

Stanley Chan
37A Tampines Street
-
Singapore Singapore 528886
Phone: +49-9287-71-2787
Fax:
-

Description of Change: To consolidate the production processes we will discontinue some T&R packaging options from the CeraMite brand. Please check in this PTN for available options in bulk packaging.

Reason for Change: Consolidation of production processes.

Expected Influence on Quality/Reliability/Performance: NA

Part Numbers/Series/Families Affected: Please see materials list on the succeeding page.

Vishay Brand(S): Vishay Cera-Mite

Time Schedule:

Last Time Buy Date: Sunday November 22, 2026

Last Time Ship Date: Sunday May 23, 2027

Sample Availability: NA

Product Identification: by PN

Qualification Data: NA

This PTN is considered approved, without further notification, unless we receive specific customer concerns before Monday June 15, 2026 or as specified by contract.

Issued By: Florian Weyland, florian.veyland@vishay.com



The DNA of tech.™

Product Termination Notification



Product Group: CC/Thursday May 21, 2026/PTN-CC-00004-2026-REV-0

125LS22XK-R	25YD10VZ-R	25YD22QT-R	30LVQ22QT-R	30LVSS10QQ-R
30LVT47QL-R	440LD47XT-R	440LS10QQ-R	440LT68AP-R	561R10TCCQ20QA
561R10TCCQ22TR	561R10TSQ30RR	561R1DF0T47LB	561RU2JQA102EC200K	562R10TSD10RE
562R10TSD10TR	562R10TST15VE	562R10TST25QA	562R10TST47RE	562R10TST56QR
562R10TST68RE	562R5GAD10RE	562R5GAD10TR	562R5GAD50RE	562R5GAS10TR
562R5GAS20QM	562R5GAT10TR	562R5GAT50QA	562R5HKMS10RK	562R5HKMS10RR
562R5HKZS10RE	562R5TSD22TR	562RX5FQA102EE102M	562RX5FRE102EE221K	562RZ5URR102EH103Z
564R20TSD10RT	564R20TSD15QA	564R30GAD10KA	564R30GAD10WN	564R30TSD10QY
564R30TSD10WN	565R30GASS20Z7A			

Parts on EOL	Material Description (EOL parts)	Active parts/orderable	Material Description (active parts)
25YD10VZ-R	25YD X400 Y250VAC 1000pF±20%Y5S T&R&R e3	25YD10-R	25YD X400 Y250VAC 1000pF ±20% Y5S BULK e3
25YD22QT-R	25YD X400 Y250VAC 2200pF±20% Y5S T&R e3	25YD22-R	25YD X400 Y250VAC 2200pF±20% Y5S BULK e3
30LVQ22QT-R	30LV X400 Y300VAC 22pF±10% N1500 T&R e3	30LVQ22-R	30LV X400 Y300VAC 22pF±10% N1500 BULK e3
30LVT47QL-R	30LV X400 Y300VAC 470pF ±10% X7R T&R&Re3	30LVT47-R	30LV X400 Y300VAC 470pF±10% X7R BULK e3
561R10TCCQ20QA	561R 1KVDC 20pF ±5% NP0 T&R e3	561R10TCCQ20	561R 1KVDC 20pF ±5% NP0 BULK e3
561R10TCCQ22TR	561R 1KVDC 22PF ±5% NP0 T&R&R e3	561R10TCCQ22	561R 1KVDC 22pF ±5% NP0 BULK e3
561R10TSQ30RR	561R 1KVDC 30pF ±10% U2J T&R e3	561R10TSQ30	561R 1KVDC 30pF ±10% U2J BULK e3
561R1DF0T47LB	561R 1KVDC 470pF ±10% N2800 T&R e3	561R1DF0T47	561R 1KVDC 470pF ±10% N2800 BULK e3
562R10TSD10RE	562R 1KVDC 1000pF ±10% X5F T&R e3	562R10TSD10	562R 1KVDC 1000pF ±10% X5F BULK e3
562R10TSD10TR	562R 1KVDC 1000PF ±10% X5F T&R&R e3	562R10TSD10	562R 1KVDC 1000pF ±10% X5F BULK e3
562R10TST15VE	562R 1KVDC 150pF ±10% X5F T&R&R e3	562R10TST15	562R 1KVDC 150pF ±10% X5F BULK e3
562R10TST25QA	562R 1KVDC 250PF ±10% X5F T&R e3	562R10TST25	562R 1KVDC 250pF ±10% X5F BULK e3
562R10TST47RE	562R 1KVDC 470PF ±10% X5F T&R e3	562R10TST47	562R 1KVDC 470pF ±10% X5F BULK e3
562R10TST56QR	562R 1KVDC 560pF ±10% X5F T&R&R e3	562R10TST56	562R 1KVDC 560pF ±10% X5F BULK e3
562R10TST68RE	562R 1KVDC 680pF ±10% X5F T&R e3	562R10TST68	562R 1KVDC 680pF ±10% X5F BULK e3
562R5GAD10RE	562R 1KVDC 1000pF ±20% X7R T&R&R e3	562R5GAD10	562R 1KVDC 1000pF ±20% X7R BULK e3
562R5GAD10TR	562R 1KVDC 1000pF ±20% X7R T&R&R e3	562R5GAD10	562R 1KVDC 1000pF ±20% X7R BULK e3
562R5GAS10TR	562R 1KVDC 10000pF ±20% Z5U T&R&R e3	562R5GAS10	562R 1KVDC 10000PF ±20% Z5U BULK e3
562R5GAT10TR	562R 1KVDC 100pF ±20% X5F T&R&R e3	562R5GAT10	562R 1KVDC 100PF ±20% X5F BULK e3
562R5GAT50QA	562R 1KVDC 500pF ±20% X5F T&R e3	562R5GAT50	562R 1KVDC 500pF ±20% X5F BULK e3
562R5HKMS10RK	562R 1KVDC 10000PF ±20% Z5U T&R e3	562R5HKMS10	562R 1KVDC 10000PF ±20% Z5U BULK e3
562R5HKMS10RR	562R 1KVDC 10000PF ±20% Z5U T&R&R e3	562R5HKMS10	562R 1KVDC 10000PF ±20% Z5U BULK e3
562R5HKZS10RE	562R 1KVDC 10000PF -20+80% Z5U T&R e3	562R5HKZS10	562R 1KVDC 10000PF -20+80% Z5U BULK e3
562R5TSD22TR	562R 500VDC 2200pF ±10% X7R T&R&R e3	562R5TSD22	562R 500VDC 2200pF ±10% X7R BULK e3
564R20TSD10RT	564R 2KVDC 1000pF ±10% X7R T&R&R e3	564R20TSD10	564R 2KVDC 1000pF ±10% X7R BULK e3
564R20TSD15QA	564R 2KVDC 1500pF ±10% X7R T&R e3	564R20TSD15	564R 2KVDC 1500pF ±10% X7R BULK e3
564R30GAD10KA	564R 3KVDC 1000pF ±20% Z5U T&R e3	564R30GAD10	564R 3KVDC 1000pF ±20% Z5U BULK e3
564R30GAD10WN	564R 3KVDC 1000PF ±20% Z5U T&R e3	564R30GAD10	564R 3KVDC 1000pF ±20% Z5U BULK e3
564R30TSD10QY	564R 3KVDC 1000pF ±10% X7R T&R e3	564R30TSD10	564R 3KVDC 1000pF ±10% X7R BULK e3
564R30TSD10WN	564R 3KVDC 1000PF ±10% X7R T&R E3	564R30TSD10	564R 3KVDC 1000pF ±10% X7R BULK e3
562R5GAD50RE	562R 1KVDC 5000PF ±20% Z5U T&R e3	562R5GAD50	562R 1KVDC 5000pF ±20% Z5U BULK e3
565R30GASS20Z7A	565R 3KVDC 20000pF ±20% Z5U T&R e3	565R30GASS20	565R 3KVDC 20000pF ±20% Z5U BULK e3
125LS22XK-R	125L X400 Y125VAC 22nF±20% Y5V T&R&R e3	125LS22-R	125L X400 Y125VAC 22nF±20% Y5V BULK e3
30LVSS10QQ-R	30LV X400 Y250VAC 10nF±20% Y5U T&R e3	30LVSS10-R	30LV X400 Y250VAC 10nF±20% Y5U BULK e3
440LD47XT-R	440L X760 Y500VAC 4700pF±20%Y5U T&R&R e3	440LD47-R	440L X760 Y500VAC 4700pF±20% Y5U BULK e3
440LS10QQ-R	440L X760/Y500VAC 10000PF±20% Y5U T&R e3	440LS10-R	440L X760 Y500VAC 10nF±20% Y5U BULK e3
440LT68AP-R	440L X760 Y500VAC 680pF±20% Y5U T&R&R e3	440LT68-R	440L X760 Y500VAC 680pF±20% Y5U BULK e3
562R5GAS20QM	562R 1KVDC 20000pF ±20% Z5U T&R e3	562R5GAS20	562R 1KVDC 20000pF ±20% Z5U BULK e3