


Measuring leads

BNC AL 0,64



Product	BNC AL 0,64
description	BNC - adapter lead with insulated socket for 0.64 mm round pillar and 0.64 mm rectangular pillar. Red inner lead, black shielding, for use with oscilloscopes, PC-card, ... cable typ: RG 58 A/U, 50 Ohm
operating instruction	BA001
Articlenumber	933844001
drawing	
	
technical data	
rated voltage	30 VAC / 60 VDC
temperature range acc. To IEC61010 ⁽¹⁾	-15 °C to +70 °C
cable length	120 cm

⁽¹⁾contact the manufacturer for applications at deviating temperature ranges
 stand : November 13, 2025 5:59 PM

0.64 mm system