

Set

PMS SKS



Product	PMS SKS
description	Test equipment set Standard for 4 mm system. - KLEPS 30 Clamp-type test probe with rotating grip jaws and flexible shaft for clamping of pins and wires up to $\varnothing$ 4 mm. - AK 2 S Insulated alligator clip for clamping of finest wires, clamping range up to a maximum of 9.5 mm bolt diameter. - PRUEF 2 Test probe with slender stainless steel tip for penetration of insulation and oxide layers. - MLN x/1 Measuring lead with 4 mm plug and 4 mm socket for tower construction on both sides. (length: 50 cm, 100 cm, 200 cm) Please find further technical details on individual product data sheets.
Articlenumber	932794001
technical data	
scope of delivery	1 x measuring lead MLN 50/1 black (934 060-100) 1 x measuring lead MLN 50/1 red (934 060-101) 2 x measuring lead MLN 100/1 black (934 062-100) 2 x measuring lead MLN 100/1 red (934 062-101) 1 x measuring lead MLN 200/1 black (934 065-100) 1 x measuring lead MLN 200/1 red (934 065-101) 1 x clamp-type test probe KLEPS 30 black (930 113-100) 1 x clamp-type test probe KLEPS 30 red (930 113-101) 1 x crocodile clip AK 2 S black (932 146-100) 1 x crocodile clip AK 2 S red (932 146-101) 1 x test probe PRUEF 2 black (973 368-100) 1 x test probe PRUEF 2 red (973 368-101)

stand : November 13, 2025 5:59 PM

4 mm system