

Set

**PMS SKS Elektronik**



| Product           | PMS SKS Elektronik                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                     |
|-------------------|----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| description       | <p>Service Case electronic for all tasks of development, service, education and more.</p> <ul style="list-style-type: none"> <li>- PRUEF 2610 FT - safety-test probe, shatter-proof insulated sleeve with slender, spring-loaded stainless steel tip</li> <li>- MICRO-PRUEF MPS 2 0.64 FT - miniature test probe with slender, spring-loaded stainless steel tip, for sampling of SMD components</li> <li>- MICRO-KLEPS - miniature test clips with 0,64mm connecting plugs and rotating gripper (SMD technology)</li> <li>- KLEPS 064 PCH - miniature test clips with 0,64mm plug for tapping from pins and wires up to Ø 1mm</li> <li>- MZS 4 - overmolded plug adapter from 4mm plug to 2mm socket</li> <li>- MICRO-SMD CLIP 1 - two-pole test clip for SMD components with flat gripper, electrically insulated spring and 0,64mm sockets</li> <li>- MA 260 SH - safety miniature alligator clip with 4mm connecting socket, clamping distance: fine wires up to Ø 6mm</li> <li>- AK 2 B 2540 I - wide-opening, contact protected alligator clip, for bolt diameter up to 30mm</li> <li>- MLS WS 50/2.5 - safety-test lead, both sides with Ø 4mm stackable safety plugs (length: 50 cm)</li> <li>- MAL N 4-0.64/100-0.25 - overmolded test lead with 4mm spring-loaded plug with onward connection capability and 0,64mm insulated connecting socket (length: 100 cm)</li> <li>- MKL 0.64/25-0.25 - test lead, on both sides 0,64mm insulated connecting sockets (length: 25 cm)</li> <li>- BNC AL 0.64 - BNC adapter cable with two insulated 0.64 mm connecting sockets for measuring</li> <li>- 2-footer-positioner</li> </ul> |
| Articlenumber     | 932791001                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                              |
| technical data    |                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                        |
| scope of delivery | <p>           1x test probe PRUEF 2610 FT black (972 318-100)<br/>           1x test probe PRUEF 2610 FT red (972 318-101)<br/>           1x test probe MICRO-PRUEF MPS2 0,64FT black (973 995-100)<br/>           1x test probe MICRO-PRUEF MPS2 0,64FT red (973 995-101)<br/>           1x clamp-type test probe MICRO-KLEPS black (973 972-100)<br/>           1x clamp-type test probe MICRO-KLEPS red (973 972-101)<br/>           1x clamp-type test probe KLEPS 064 PCH black (974 201-100)<br/>           1x KLEPS 064 PCH red (974 201-101)<br/>           1x KLEPS 064 PCH blue (974 201-102)<br/>           1x KLEPS 064 PCH yellow (974 201-103)<br/>           1x KLEPS 064 PCH green (974 201-104)<br/>           1x KLEPS 064 PCH grey (974 201-106)         </p>                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                       |

|                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                               |
|-----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| 1x KLEPS 064 PCH white (974 201-107)<br>1x plug MZS 4 black (973 599-100)<br>1x plug MZS 4 red (973 599-101)<br>1x MICRO-SMD CLIP 1 (972 416-100)<br>1x crocodile clip MA 260 SH black (973 889-100)<br>1x crocodile clip MA 260 SH red (973 889-101)<br>1x crocodile clip AK 2B 2540I yellow/green (972 405-188)<br>1x test lead MLS WS 50/2,5 black (934 087-100)<br>1x test lead MLS WS 50/2,5 red (934 087-101)<br>1x test lead MLS WS 50/2,5 yellow/green (934 087-188)<br>1x test lead MAL N4-0,64/100-0,25 black (934 160-100)<br>1x test lead MAL N 4-0,64/100-0,25 red (934 160-101)<br>1x test lead MKL 0,64/25-0,25 black (973 604-100)<br>1x test lead MKL 0,64/25-0,25 red (973 604-101)<br>1x test lead BNC AL 0,64 black (933 844-001)<br>1x 2-footer-positioner (974 401-000) |
|-----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|

stand : November 13, 2025 5:59 PM