


Plugs

KST S WS



Product	KST S WS
description	Touch protected shorting plug with caged spring and unsprung socket, with onward connection capability and shatter-proof insulated sleeve.
operating instruction	BA462
article-no. / *colour	9322001xx  00 black  01 red  02 blue  03 yellow  04 green  05 brown  06 gray  07 white  09 violet  88 yellow/green
drawing	
	
technical data	
connection	unsprung socket 4 mm
rated voltage	AC/DC 1000 V
measurement cat. acc. to IEC 61010	CAT II
rated current (consider derating curve)	32 A
material plug	brass, nickel plated
housing material	PA
temperature range acc. To IEC61010 ⁽¹⁾	-15 °C to +70 °C
flammability class acc. to UL 94 (only valid for basic material of housing)	V-2

⁽¹⁾contact the manufacturer for applications at deviating temperature ranges
 stand : November 13, 2025 6:00 PM