

Product Information

97 52 63 DG A

Four-Mandrel Crimping Pliers for turned con-
tacts



- Basic pliers without locator for crimping turned pin and socket contacts from various manufacturers with 0.08–2.5 mm² (AWG 28–14)
- Crimp mandrel feed adjustable in increments of 0.01 mm and digitally readable; setting in mm, inch or comparable selector settings according to MIL standard
- Electronic wear monitoring (patented) with warning function
- Reliable crimping thanks to synchronised feed of the crimping mandrels
- Process-secure and consistently high crimp quality thanks to IEC 60352-compliant trigger lock (positive lock, can be unlocked)
- With recalibration function; check basic setting using the enclosed test pin
- The range of applications of the crimping pliers can be extended by exchanging the contact holders of various contact manufacturers
- High operation comfort thanks to handy shape
- Pliers in plastic case with foam tray, gauge pin for checking the basic setting and slots for up to 3 optional locators from the 97 59 63/65 xxx series

General	
Part No.	97 52 63 DG A
EAN	4003773093572
Pliers	chrome-plated
Head	chrome-plated
Handles	with multi-component handles
Weight	855 g
Dimensions	175 x 220 x 52 mm
REACH compliant	does not contain SVHC
RoHS compliant	not applicable
Technical details	
Application	turned contacts
Capacity in square millimetres	0.08 – 2.5 mm ²
AWG	28 – 14
Max. contact diameter	5 mm

Technical changes and errors excepted

