



# PRODUCT SPEC SHEET

**SKU 801-27**

**Model:VT-8603**

**EAN:3800170254848**

## VT-8603 8W/16W/20W LED DOME LIGHT 3IN1 RD IP65



**IP65**  
STANDARD

**05**  
YEAR  
WARRANTY

Super Bright  
**120**  
LUMENS/W

- CCT Bulkhead with High Quality In Build Power Driver
- Easily switch to preferred wattage 8W, 16W, 20W
- Built in switch for CCT changing
- IP65 Ingress protection
- IK protection IK08
- Lumen output ranging from 1050lm-2600lm on preferred wattages
- Side conduit entry for easy installation
- Applications - Passage, Exterior walls, Airport, Malls, roof, fence etc

## TECHNICAL INFORMATION

|                           |                   |
|---------------------------|-------------------|
| <b>Color Temperature:</b> | 3IN1              |
| <b>Model:</b>             | VT-8603           |
| <b>Dimmable:</b>          | No                |
| <b>CRI:</b>               | >80               |
| <b>Watts:</b>             | 20                |
| <b>Lumens:</b>            | 2600              |
| <b>Input Power:</b>       | AC:200-240V, 50Hz |
| <b>Unit Color:</b>        | White             |
| <b>Color for Web:</b>     | 3IN1              |
| <b>Body Type:</b>         | PC                |
| <b>Dimension:</b>         | 320x100mm         |
| <b>Shape:</b>             | Round             |
| <b>PF:</b>                | >0.9              |
| <b>LED Chip Type:</b>     | SMD               |

## LISTING DETAILS

|                        |               |
|------------------------|---------------|
| <b>SKU:</b>            | 801-27        |
| <b>Model:</b>          | VT-8603       |
| <b>EAN:</b>            | 3800170254848 |
| <b>Commodity Code:</b> | 94051140      |

## PACKAGING

|                            |           |
|----------------------------|-----------|
| <b>Gross Weight (Kgs):</b> | 1.23      |
| <b>Unit CBM:</b>           | 0.013566  |
| <b>Dimension:</b>          | 320x100mm |

## MASTER BOX PACKAGING

|                         |     |
|-------------------------|-----|
| <b>Box Qty:</b>         | 10  |
| <b>Qty Per Pallet:</b>  |     |
| <b>Length (Box) mm:</b> | 330 |

|                      |              |
|----------------------|--------------|
| Beam Angle:          | 110°         |
| Energy Rating Label: | E (2021)     |
| IP Rating:           | IP65         |
| IK Rating:           | IK08         |
| Long Life:           | 30,000 Hours |
| lumens per watt:     | 120          |

|                  |     |
|------------------|-----|
| Width (Box) mm:  | 110 |
| Height (Box) mm: | 330 |