



PRODUCT SPEC SHEET

SKU 216976

Model:VT-125

EAN:3800170256187

VT-125 16W T5 LED BATTEN FITTING CREE CHIP 6500K 6 YEARS WARRANTY



IP20
STANDARD



- Introducing T5 Integrated Fittings designed with ON/OFF Switch.
- Linkable feature allowing you to link up to 100 watts together in series
- Fitted with high efficiency SMD-CREE Chip that offer up to 85% in energy savings
- Switch cycles: >15000
- Suitable for residential and commercial applications.

TECHNICAL INFORMATION

Color Temperature:	6500K
Model:	VT-125
On/Off Cycles:	>15000
Dimmable:	No
CRI:	>80
Watts:	16
Lumens:	1600
Input Power:	AC:220-240V, 50Hz
Unit Color:	White
Color for Web:	White
Body Type:	Plastic
Dimension:	1151x27x30mm
Operation Temperature:	-20°C to +40°C
Shape:	T5

LISTING DETAILS

SKU:	216976
Model:	VT-125
EAN:	3800170256187
Commodity Code:	94054210

PACKAGING

Gross Weight (Kgs):	0.24
Unit CBM:	0.00153
Dimension:	1151x27x30mm

MASTER BOX PACKAGING

Box Qty:	25
Qty Per Pallet:	600
Length (Box) mm:	1230

PF:	>0.7
LED Chip Type:	SMD-CREE Chip
Beam Angle:	160°
Energy Rating Label:	F (2021)
Linkable:	Upto 100W Max
IP Rating:	IP20
IK Rating:	IK04
Energy Saving:	85 Energy
Long Life:	30,000 Hours
lumens per watt:	100

Width (Box) mm:	33
Height (Box) mm:	30