



# PRODUCT SPEC SHEET

**SKU 242816**

**Model:VT-9-157**

**EAN:3800170259546**

## VT-9-157 150W/200W/240W LED HIGHBAY CREE CHIP SOSEN DRIVER 3IN1 160LM/W 6YRS WTY



**IP65**  
STANDARD



- New 3IN1 Color Changeable Linear Highbay with CREE Chip
- Power Selectable – Choose between 150W/200W/240W output to match your lighting requirements
- CCT and Power Changeable using DIP switch
- Fitted with high efficiency SMD-CREE Chip and SOSEN Driver
- Linear Highbay designed with a Lumen efficiency of 160LM/W
- Strong and sturdy PC+AL built with IK06 rated protection
- Suitable for commercial lighting, office, supermarkets, shop, hotels & similar environment

## TECHNICAL INFORMATION

|                               |                      |
|-------------------------------|----------------------|
| <b>Color Temperature:</b>     | 3IN1                 |
| <b>Model:</b>                 | VT-9-157             |
| <b>Instant Start:</b>         | 0-100% in <1s        |
| <b>CRI:</b>                   | >80                  |
| <b>Watts:</b>                 | 240                  |
| <b>Lumens:</b>                | 32000                |
| <b>Input Power:</b>           | AC:220-240V, 50/60Hz |
| <b>Unit Color:</b>            | Black                |
| <b>Color for Web:</b>         | 3IN1                 |
| <b>Body Type:</b>             | PC+AL                |
| <b>Dimension:</b>             | 1060x101x65mm        |
| <b>Operation Temperature:</b> | -20°C to +40°C       |

## LISTING DETAILS

|                        |               |
|------------------------|---------------|
| <b>SKU:</b>            | 242816        |
| <b>Model:</b>          | VT-9-157      |
| <b>EAN:</b>            | 3800170259546 |
| <b>Commodity Code:</b> | 94054210      |

## PACKAGING

|                            |               |
|----------------------------|---------------|
| <b>Gross Weight (Kgs):</b> | 3.04          |
| <b>Unit CBM:</b>           | 0.010781      |
| <b>Dimension:</b>          | 1060x101x65mm |

## MASTER BOX PACKAGING

|                        |   |
|------------------------|---|
| <b>Box Qty:</b>        | 6 |
| <b>Qty Per Pallet:</b> |   |

|                      |               |
|----------------------|---------------|
| PF:                  | >0.9          |
| LED Chip Type:       | SMD-CREE Chip |
| Beam Angle:          | 90°           |
| Energy Rating Label: | D (2021)      |
| IP Rating:           | IP65          |
| IK Rating:           | IK06          |
| Energy Saving:       | 85 Energy     |
| Long Life:           | 50,000 Hours  |
| lumens per watt:     | 160           |

|                  |      |
|------------------|------|
| Length (Box) mm: | 1095 |
| Width (Box) mm:  | 103  |
| Height (Box) mm: | 69   |