



PRODUCT SPEC SHEET

SKU 972126

Model:VT-48500

EAN:3800170254619

VT-48500 500W SUPER HIGH POWER FLOODLIGHT CREE CHIP 1M WIRE 6500K BLACK BODY 135LM/W 6YRS WTY IP65



IP65
STANDARD



- High performance light for outdoor applications
- Product designed with high lumen efficiency of 135 LM/W
- High quality LED SMD-CREE Chip
- IP65 rated outdoor protection with a warranty period of 6 Years
- Experience hassle-free setup with the provided 1-meter cable
- Built Strong and durable with Diecast Aluminium - Corrosion resistant design
- Suitable for building facades, sports facilities, industrial, commercial billboards, hoardings, parking lots etc.

TECHNICAL INFORMATION

Color Temperature:	6500K
Model:	VT-48500
Instant Start:	< 1 Sec
On/Off Cycles:	>15000
Dimmable:	No
CRI:	>70
Watts:	500
Lumens:	67500
Input Power:	AC:220-240V, 50Hz
Unit Color:	Black
Color for Web:	White
Body Type:	Diecast Aluminium
Dimension:	530x65x523mm

LISTING DETAILS

SKU:	972126
Model:	VT-48500
EAN:	3800170254619
Commodity Code:	94054210

PACKAGING

Gross Weight (Kgs):	9.03
Unit CBM:	0.046405
Dimension:	530x65x523mm

MASTER BOX PACKAGING

Box Qty:	1
Qty Per Pallet:	30

Operation Temperature:	-20°C to +45°C
PF:	>0.9
LED Chip Type:	SMD-CREE Chip
Beam Angle:	60°
Energy Rating Label:	D (2021)
Wire Length:	1m
IP Rating:	IP65
IK Rating:	IK05
Energy Saving:	85 Energy
Long Life:	30,000 Hours
lumens per watt:	135

Length (Box) mm:	600
Width (Box) mm:	595
Height (Box) mm:	130