


Technical Attributes RF Cable / Technische Daten RF-Kabel

Mechanical characteristics	Mechanische Eigenschaften	
cable weight	Kabelgewicht	35 kg/ km
minimum bend radius	Mindestbiegeradius	
single bend	Einmalig	30 mm
multiple bend	Mehrfach	50 mm
Environmental	Umgebung	
operating temp.	Betriebstemperatur	-30°C / +70°C
flame retardant acc.	schwerentflammbar gemäß	IEC 60332-1-2
UL-Style	UL-Style	MIL C 17
RoHS compliant	RoHS konform	2011/ 65/ EU
Electrical characteristics	Elektrische Eigenschaften	
impedance	Wellenwiderstand	50 ±3 Ω
capacitance	Kapazität	103 pF/ m
working voltage	Betriebsspannung	300 V (peak)
voltage proof	Prüfspannung	2 kV eff.
velocity ratio	Verkürzungsfaktor	66 %

Änd./ rev. index	Änderungs-Nr. / revision code	Datum/ date	Name/ name		Datum/ date	Name/ name	Gewicht/ weight [g] ca./approx.	
				gez./ drawn	09.06.2026	JA		
				gepr./ appr.	24.06.2026	SKH		
-	500000002580	15.06.2026	JA	Maßstab/ scale	Benennung/ title			 Telegärtner
				1:45:	CXA RG-58PVC BNC Plg 2xBanana Plg 0,5m			
					CXA RG-58PVC BNC Plg 2xBanana Plg 0,5m			
				untol. Maße/ dim. without tolerances according to	Unterf./ doc. type	Materialnr./ material no.		 Maße/ dimensions: mm
				CUG	100009738			
				Ersatz für/ replaces	PDM Nr./ pdm no. 10025668			
								Original : DIN A3
								Blatt/ sheet 1 von/ of 1