


AOHA21AA010 Datasheet

Product Name // Active Optical HDMI 2.1 Type A - Type A
Cable 10m

 [View Product Page](#)



// Product Description:

- Standard PVC Jacket
 - 8K@60Hz
 - 48Gbps
- Low Power consumption 250mW (max)
 - Hybrid type with OM3 fiber and copper wire
 - 10m

// General Information:

Product Display Title:	AO Series HDMI 2.1 Type A -Type A Cable 10m
Product Family:	Data Connectors
Product Series:	AO Series Active Optical HDMI
Body Colour:	Matt Black
Body Material Type:	Metal
Cable Length:	10m
Data Cable Type:	HDMI
Fibre Mode:	Multimode
Flamability Rating:	VW-1
Function:	Active Optical HDMI Cable
Material Finish:	Matt
Max Operating Temperature:	50°C
Min Operating Temperature:	0°C
Operating Humidity:	10~80 %RH
Rohs Compliant:	Yes

// Product PDF Links



// Product 3D CAD Model Links



Have a question or project enquiry
you'd like to talk to us about?



[Click Here To Contact Us](#)