




EH CONNECTOR



2.5mm Pitch/Wire-to-Board Connectors/Crimp Style and Mating Style



Part Number:

- ASEHSEH22K254

Description:

- JST Series – [EH Series](#)
- Pitch – 2.5mm
- Cable length (inside dimension) – 254mm

Material Specification:

- (1) Terminal: SEH-001T-P0.6
- (2) Cable Type: UL1007
- (2) Cable Size: 22AWG
- (2) Cable Colour: Black

Accessories:

- Extraction Tool: EJ-PH

Quality

- We trust and believe in our product. Each step of our development and manufacturing process is focused on delivering a fault-free product. JST does not compromise on quality.

Applicable Housings:

No. of Circuits	Part Number
2	EHR-2
3	EHR-3
4	EHR-4
5	EHR-5
6	EHR-6
7	EHR-7
8	EHR-8
9	EHR-9
10	EHR-10
11	EHR-11
12	EHR-12
13	EHR-13
14	EHR-14
15	EHR-15

Additional Information:


Alternative Colours and length cables are available upon request, please contact JST for further details by e-mailing jukma@jst.co.uk



EH CONNECTOR



2.5mm Pitch/Wire-to-Board Connectors/Crimp Style and Mating Style



A SEH SEH 22 K 254

Supply Form: Assembled Wire

Terminal Part Number end A: SEH-001T-P0.6

Terminal Part Number end B: SEH-001T-P0.6

Cable Size: 22awg (??AWG)

Cable Colour: B (Blue), K (Black), R (Red), N (Brown), H (Grey)
O (Orange), Y (Yellow), W (White), M (Green), P (Purple), PK (Pink)

Cable Length: 254mm (????mm)

Additional Information:

Alternative Colours and length cables are available upon request, please contact JST for further details by e-mailing jukma@jst.co.uk