

KEW8035

Non-contact Phase Rotation Tester

PRODUCT DATA SHEET

KEW8035

- Unique technology permits safe testing, without the need of direct contact between probes and live wires.
- The insulated crocodile clips can clip insulated cables from $\phi 2.4$ to 30mm.
- Phase rotation is indicated by the rotary illumination of LEDs and logical audible tones.
- The instrument can be fixed to a metal panel via the magnet on the back side.
- Wide measuring range for 3 phase installations from 70V to 1000V AC.
- Complies with IEC61010-1 CAT.IV 600V and CAT.III 1000V.



SPECIFICATION

Functions	Phase rotation (Clockwise or Counter Clockwise), Presence of open phase
Detection Method	Electrostatic induction
Measuring Voltage Range	From 70 to 1000V AC phase to phase (sine wave, continuous input)
Clamp Diameter Range	From $\phi 2.4$ to 30mm insulated cables
Measuring Frequency Range	45 to 66Hz
Phase Rotation	Clockwise: Green arrow LEDs 'rotate' in clockwise, Green symbol 'CW' lits, intermittent buzzer Counter Clockwise: Red arrow LEDs 'rotate' in counter clockwise, Red symbol 'CCW' lits, continuous buzzer
Visual Indication	Via LEDs with Super brightness function
Operation Conditions	Temperature/Humidity Ranges -10 to 50°C, 80% (no condensation)
Storage Conditions	Temperature/Humidity Ranges -20 to 60°C, 80% (no condensation)
Power Supply	Alkaline battery(LR6)x4 • Continuous use: approx. 100 hours (auto power off in 10 min.)
Battery Voltage Warning	Power LED blinks if battery voltage is too low
Test Leads	Double insulated cables, lenght approx.
Colours Code	L1(U): Red L2(V): White L3(W): Blue
Applicable Standards	IEC 61010-1 CAT.IV 600V, CAT.III 1000V Pollution degree2, IEC 61557-1, -7
Dimensions/Weight	112(L)x61(W)x36(D)mm / Approx. 380g

PRODUCT INFO

- 170 x 187 x 190 Boxed (WxDxH mm)
- 0.62kg Weight
- EAN 4560187064227
- Made in Thailand