

2 Port DVI Video Splitter with Audio - TAA

Product ID: ST122DVIA



The ST122DVIA DVI splitter lets you share one DVI video and audio source on two displays and acts as a signal amplifier that allows you to locate your DVI monitors up to 33ft (10 m) away from your computer or DVI signal source.

With support for high definition resolutions up to 1080p (HDTV)/1920x1200 (PC), the DVI splitter delivers a simple and convenient DVI video solution that suits virtually any application or operating environment (classroom, healthcare, professional A/V, control centres, retail POS environments).

The DVI video splitter/distribution amplifier is easy to install, providing you with flawless digital video that will help you get the most from your DVI-enabled monitors, projectors, or plasma screens.

This product is TAA compliant and backed by StarTech.com's 2-year warranty with FREE lifetime tech support.

Certifications, Reports and Compatibility



Applications

- Connect DVI projectors, monitors, large displays, and wall display systems for digital signage applications and ensuring content is delivered to target audience.
- Great for use in tradeshows, POS retail, healthcare, transportation terminals, education, house of worship.

Features

- Supports resolutions of up to 1920 x 1200 pixels @ 60 Hz
- Split both video and 3.5mm analog stereo audio
- DVI, and HDCP compliant for easier HD video distribution
- Accurate and reliable reproduction of digital video signal, with no signal attenuation or distortion
- Easy setup for a quick connection in minutes

General

UPC	065030839563
Package Quantity	1
Warranty	2 Years

Power

Power Source	AC Adapter Included
Input Current	0.6A
Output Voltage	12V DC
Output Current	1.5
Center Tip Polarity	Positive
Plug Type	M
Power Consumption	18W

Physical & Environmental

Color	Black
Material	Aluminum
Product Length	7.1 in [18.1 cm]
Product Width	3.4 in [85.2 mm]
Product Height	0.8 in [20.0 mm]
Weight of Product	14.2 oz [401.0 g]
Operating Temperature	0C to 40C (32F to 104F)
Storage Temperature	-20C to 60C (-4F to 140F)

Humidity 0~80% RH

Performance

Max Distance 10m [33ft]

Maximum Digital Resolutions 1920x1200 @ 60Hz

Wide Screen Supported Yes

Hardware

AV Input DVI

Number of Ports 2

AV Output DVI

Cabling DVI

Industry Standards DVI 1.0, and HDCP 1.1

LED Indicators 1 - Green - Power/Link

2 - Green - Link

Packaging & In-the-Box

Included in Package 1 - DVI splitter

4 - rubber feet

1 - universal power adapter (NA, EU, UK, ANZ)

1 - instruction manual

Package Width 8.7 in [22.1 cm]

Package Depth 3.9 in [100 mm]

Package Height 3.9 in [100 mm]

Shipping (Package) Weight 25.3 oz [716 g]

Connector(s)

Connector 1 (Quantity) 1

Connector 1 DVI-I Dual-Link (29-Pin)

Connector 2 (Quantity)	1
Connector 2	3.5mm (3 Conductors, TRS)
Connector 3 (Quantity)	2
Connector 3	DVI-I Dual-Link (29-Pin)
Connector 4 (Quantity)	2
Connector 4	3.5mm (3 Conductors, TRS)

****Product appearance and specifications are subject to change without notice.***