

## 12in SATA to Left Angle SATA Serial ATA Cable

**Product ID:** SATA12LA1



The SATA12LA1 Left Angle (90-degree) SATA Cable features a standard (straight) SATA receptacle as well as a left-angled SATA receptacle, providing a simple 12-inch connection to a Serial ATA drive, with full SATA 3.0 bandwidth support of up to 6Gbps when used with SATA 3.0 compliant drives.

The left-angled SATA connection enables you to plug in your Serial ATA hard drive in hard to reach areas or tight spaces, while the low profile and flexible design of the cable improves airflow and reduces clutter in your computer case, helping to keep the case clean and cool.

Constructed of only top quality materials and designed for optimum performance and reliability this 12" SATA cable is backed by our lifetime warranty.

As an alternative, StarTech.com also offers a SATA12RA1 (SATA12RA1), which provides the same simple installation as this left angled SATA cable, but allows the cable to connect to the SATA drive from the opposite direction.

## Certifications, Reports and Compatibility



## Applications

- Installing Serial ATA hard drives, and DVD drives in Small Form Factor computer cases
- Server and storage subsystem applications
- High-end workstation drive installations

- Connections to SATA Drive Arrays

## Features

- 1x SATA connector
- 1x Left-angled/90-degree SATA connector
- Supports full SATA 3.0 6Gbps bandwidth
- Compatible with both 3.5" and 2.5" SATA hard drives
- Provides 12" in cable length

---

### General

|                  |              |
|------------------|--------------|
| UPC              | 065030842723 |
| Package Quantity | 1            |
| Warranty         | Lifetime     |

---

### Physical & Environmental

|                       |                           |
|-----------------------|---------------------------|
| Color                 | Red                       |
| Connector Style       | Straight to Left Angle    |
| Wire Gauge            | 26 AWG (0.404 mm)         |
| Cable Length          | 12.0 in [30.5 cm]         |
| Product Length        | 12.0 in [30.5 cm]         |
| Product Width         | 0.5 in [12.0 mm]          |
| Product Height        | 0.2 in [6.2 mm]           |
| Weight of Product     | 0.4 oz [12.0 g]           |
| Operating Temperature | 0C to 50C (32F to 122F)   |
| Storage Temperature   | -20C to 70C (-4F to 158F) |
| Humidity              | 0-95% relative humidity   |

---

### Performance

|                    |                   |
|--------------------|-------------------|
| SATA Type and Rate | SATA III (6 Gbps) |
|--------------------|-------------------|

---

**Hardware**

|                       |                          |
|-----------------------|--------------------------|
| Number of Conductors  | 7                        |
| Cable Jacket Material | PVC - Polyvinyl Chloride |

---

**Packaging &  
In-the-Box**

|                              |                                                   |
|------------------------------|---------------------------------------------------|
| Included in Package          | 1 - 12in SATA to Left Angle SATA Serial ATA Cable |
| Package Width                | 5.7 in [14.5 cm]                                  |
| Package Depth                | 4.9 in [12.5 cm]                                  |
| Package Height               | 0.7 in [19 mm]                                    |
| Shipping (Package)<br>Weight | 0.5 oz [14 g]                                     |

---

**Connector(s)**

|                        |              |
|------------------------|--------------|
| Connector 1 (Quantity) | 1            |
| Connector 1            | SATA (7-Pin) |
| Connector 2 (Quantity) | 1            |
| Connector 2            | SATA (7-Pin) |

---

***\*Product appearance and specifications are subject to change without notice.***