

24 Port 1U Rackmount Cat 6 110 Patch Panel

Product ID: C6PANEL24



The C6PANEL24 24-port 110-type Rack Mount Cat 6 Patch Panel is color coded for both T568A and T568B wiring providing the perfect solution for any voice or LAN application.

For hassle-free connections, the patch panel offers straight Cat 6 ports with 110-type termination, making it easy to insert and remove your cables. The 24-port patch panel also offers a quick and easy way to identify your cable runs, with port numbers clearly marked on the back of each RJ45 port, and a writeable/erasable marking surface for each port on the front of the panel for efficient system management.

Durably constructed of only top quality materials, this 24-port Network Patch Panel is backed by StarTech.com's 2-year warranty.

Certifications, Reports and Compatibility



Applications

- For installation in 19" rack/cabinets
- Suitable for applications that use 23-26 AWG solid state and standard network cables
- 1000BASE-T Gigabit Ethernet, 100BASE-TX Fast Ethernet, 10BASE-T Ethernet applications
- Voice, video and other applications

Features

- Color coded for both T568A and T568B installations
- Terminated using 110-type punch tool
- Supports both Cat5e and Cat6 cables
- Writable and erasable marking surfaces for each port
- Meeting the ANSI/TIA-568-C.2 Category 6, ISO/IEC11801 and EN50173-1 specification

General

UPC	065030857475
Package Quantity	1
Warranty	2 Years

Special Notes / Requirements

Special Notes	IDC Contact : Phosphor Bronze with Tin Plating
---------------	--

Physical & Environmental

Color	Black
Product Length	1.3 in [34.0 mm]
Product Width	19.0 in [48.3 cm]
Product Height	1.7 in [44.0 mm]
Weight of Product	20.5 oz [581.0 g]
Operating Temperature	-10~60
Humidity	10~65%

Packaging & In-the-Box

Included in Package	1 - 24 Port 1U Rackmount Cat 6 110 Patch Panel
	4 - M6 Screws
	4 - M5 Screws
Package Width	2.3 in [59 mm]

Package Depth	19.3 in [49.1 cm]
Package Height	1.9 in [47 mm]
Shipping (Package) Weight	23.1 oz [654 g]

****Product appearance and specifications are subject to change without notice.***