

Product information

97 59 65 HA1

Locator for Harting

- For four-mandrel crimping pliers for turned contacts, 0.14–6 mm² (AWG 26–10), contact diameter up to 7.5 mm
- For precise positioning of connector types HAN C / HAN D / HAN E / Yellock, see adjustment table (separate download) for details on contact series



General

Part No.	97 59 65 HA1
EAN	4003773093534
Weight	75 g
Dimensions	38 x 55 x 45 mm
REACH compliant	does not contain SVHC
RoHS compliant	not applicable

technical change and errors excepted