HellermannTyton

# Technical data sheet

## Article number:
## 133-04257 TEC70

| | |
|---|---|
| **Product Group** | Bundling clips with edge clips |
| **Product Family** | for panel thicknesses of 1.0 - 4.0 mm |
| **Material** | Polyamide 6.6, high impact modified, heat and UV-stabilised (PA66HIRHSUV), Metal (MET) |
| **Colour** | Black (BK) |

| | |
|---|---|
| **Bundle Ø max.** | 7.8 mm |
| **CE Certification** | No |
| **Fixation Method** | Edge Clip |
| **Height (H)** | 9.6 mm |
| **Length (L)** | 15.5 mm |
| **Length (L2)** | 36.2 mm |
| **Operating Temperature** | -40 °C to +105 °C |
| **Package Content** | 4000 pcs. |
| **Package Content packed in** | pack |
| **Panel Thickness** | 1.6 - 2.0 mm |
| **Panel Thickness max.** | 2.0 mm |
| **Panel Thickness min.** | 1.6 mm |
| **ROHS compliant** | Yes |
| **UV-Stabilised** | Yes |
| **Width (W)** | 9.9 mm |

RoHS

created on 10. April 2026, 4:40 am

Technical changes and errors reserved. It´s up to the customer to check the suitability for a specific application by means of tests.