
Technical data sheet

Article number:
151-00074 SOC5FT6LG



Product Group	Bundling Clips with Fir Tree, for Distance Routing
Product Family	SOC5FT6LG for distance routing 13.0 mm
Material	Polyamide 6.6, high impact modified, heat stabilised (PA66HIRHS)
Colour	Black (BK)

CE Certification	No
Fixation Method	Fir Tree
Flammability	UL 94 HB
for Hole Ø (FH)	6.1 - 6.6 mm (hexagonal), 6.5 - 7.0 mm
Height (H)	12.5 mm
Length (L)	55.0 mm
Length (L2)	21.0 mm
Operating Temperature	-40 °C to +105 °C
Package Content	500 pcs.
Package Content packed in	pack
Panel Thickness	0.7 - 5.1 mm
Panel Thickness max.	5.1 mm
Panel Thickness min.	0.7 mm
Recyclate content	0 %
ROHS compliant	Yes
UV-Stabilised	No

RoHS

created on 8. May 2026, 4:39 am

Technical changes and errors reserved. It´s up to the customer to check the suitability for a specific application by means of tests.