HellermannTyton

Technical data sheet

Article number:
151-00023 SOC6

Product Group	Bundling Clips with Fir Tree, for Distance Routing
Product Family	SOC6 for distance routing 22.0 mm
Material	Polyamide 6.6, high impact modified, heat stabilised (PA66HIRHS)
Colour	Black (BK)

CE Certification	No
Fixation Method	Fir Tree
Flammability	UL 94 HB
for Hole Ø (FH)	6.1 - 6.6 mm (hexagonal), 6.3 - 7.0 mm
Height (H)	11.4 mm
Length (L)	55.0 mm
Length (L2)	22.0 mm
Operating Temperature	-40 °C to +105 °C
Package Content	500 pcs.
Package Content packed in	pack
Panel Thickness	0.8 - 3.5 mm
Panel Thickness max.	3.5 mm
Panel Thickness min.	0.8 mm
Recyclate content	0 %
ROHS compliant	Yes
UV-Stabilised	No

RoHS

created on 5. June 2026, 5:16 am

Technical changes and errors reserved. It´s up to the customer to check the suitability for a specific application by means of tests.