# Technical data sheet

## Article number:
## 151-02587 120MINICHNLFT6.5

| | |
|---|---|
| **Product Group** | Mini cable channel family |
| **Product Family** | Modular and interchangeable cable routing system |
| **Material** | Polyamide 6.6, high impact modified, heat and UV-stabilised (PA66HIRHSUV) |
| **Colour** | Black (BK) |

| | |
|---|---|
| **CE Certification** | No |
| **Fixation Method** | Fir tree for round holes |
| **for Hole Ø (FH)** | 6.1 - 7.0 mm |
| **Length (L)** | 76.53 mm |
| **Operating Temperature** | -40 °C to +105 °C |
| **Package Content** | 856 pcs. |
| **Package Content packed in** | pack |
| **Panel Thickness** | 0.5 - 4.25 mm |
| **Panel Thickness max.** | 4.25 mm |
| **Panel Thickness min.** | 0.5 mm |
| **ROHS compliant** | Yes |
| **UV-Stabilised** | Yes |
| **Width (W)** | 19.44 mm |

RoHS

created on 8. May 2026, 4:42 am

Technical changes and errors reserved. It´s up to the customer to check the suitability for a specific application by means of tests.