HellermannTyton

Technical data sheet

Article number:
151-02600 CH20D7

Product Group	Bundling Clips with Fir Tree, for Distance Routing
Material	Polyamide 6.6 (PA66)
Colour	Black (BK)

CE Certification	No
Fixation Method	arrowhead
Flammability	UL 94 V2
for Hole Ø (FH)	6.4 - 7.0 mm
Height (H)	7.62 mm
Length (L)	50.0 mm
Length (L2)	20.0 mm
Operating Temperature	-40 °C to +85 °C
Package Content	100 pcs.
Package Content packed in	pack
Panel Thickness	0.6 - 1.4 mm
Panel Thickness max.	1.4 mm
Panel Thickness min.	0.6 mm
ROHS compliant	Yes
UV-Stabilised	No

RoHS

created on 8. May 2026, 4:36 am

Technical changes and errors reserved. It´s up to the customer to check the suitability for a specific application by means of tests.