HellermannTyton

Technical data sheet

Article number:
133-03188 PC5X3

Material	Polyamide 6.6, high impact modified, heat and UV-stabilised (PA66HIRHSUV)
Colour	Black (BK)

Bundle Ø max.	5.1 mm
Bundle Ø min.	4.7 mm
CE Certification	No
Flammability	UL 94 HB
Height (H)	9.3 mm
Length (L)	25.2 mm
Operating Temperature	-40 °C to +105 °C
Package Content	4000 pcs.
Package Content packed in	pack
ROHS compliant	Yes
UV-Stabilised	Yes
Width (W)	10.16 mm

RoHS

Technical changes and errors reserved. It's up to the customer to check the suitability for a specific application by means of tests.

created on 31. July 2026, 4:03 am