HellermannTyton

Technical data sheet

Article number:
151-01206 EC48

Product Group	Bundling Clips for Edges for Distance Routing
Product Family	Bundling Clips for Edges, 3.0 - 6.0 mm, for Distance Routing
Material	Polyamide 6.6, high impact modified, heat and UV-stabilised (PA66HIRHSUV)
Colour	Black (BK)

CE Certification	No
Fixation Method	Edge Clip
Height (H)	14.83 mm
Length (L)	50.0 mm
Length (L2)	17.25 mm
Operating Temperature	-40 °C to +105 °C
Package Content	5000 pcs.
Package Content packed in	pack
Panel Thickness	3.0 - 6.0 mm
Panel Thickness max.	6.0 mm
Panel Thickness min.	3.0 mm
ROHS compliant	Yes
UV-Stabilised	Yes
Width (W)	29.71 mm

RoHS

created on 10. April 2026, 4:46 am

Technical changes and errors reserved. It´s up to the customer to check the suitability for a specific application by means of tests.