Technical data sheet

Article number:
156-03004 IRCDSTRUT

Product Group	Heavy duty cable clamps
Product Family	screwable, Inline Ratchet Clamps
Material	Polyamide 6.6, high impact modified, heat and UV-stabilised (PA66HIRHSUV)
Colour	Black (BK)

Bundle Ø max.	51.0 mm
Bundle Ø min.	36.0 mm
CE Certification	No
Fixation Method	1-5/8 " strut attachment
Height (H)	52.4 mm
Length (L)	140.9 mm
Operating Temperature	-40 °C to +105 °C
Package Content	200 pcs.
Package Content packed in	pack
ROHS compliant	Yes
Specifications	UL2239 Conduit & Cable Hanger
UL-File Number	E523406
UV-Stabilised	Yes
Variant	Load Rating: 17 lbs, Safety Factor: 3 Pull Force Rating: 50 lbs
Width (W)	34.81 mm

HF RoHS

created on 22. May 2026, 9:18 am

Technical changes and errors reserved. It´s up to the customer to check the suitability for a specific application by means of tests.