HellermannTyton

Technical data sheet

Article number:
151-03123 RCF180SM10SS

Product Group	Ratchet P-Clamp
Product Family	For bundle diameters from 63.0 mm up to 80.0 mm, F-Series
Material	Polyamide 6.6, high impact modified, heat and UV-stabilised (PA66HIRHSUV), Stainless Steel (SS304)
Colour	Black (BK)

Bundle Ø max.	80.0 mm
Bundle Ø min.	63.0 mm
CE Certification	No
Fixation Method	Screw Mounting
Flammability	UL 94 HB
for Hole Ø (FH)	10.29 mm
Length (L)	243.0 mm
Length (L2)	147.9 mm
Min.Tensile Strength	445 N
Operating Temperature	-40 °C to +105 °C
Package Content	90 pcs.
Package Content packed in	pack
ROHS compliant	Yes
UV-Stabilised	Yes
Variant	Short
Width (W)	34.9 mm

HF ✓ RoHS ✓

created on 8. May 2026, 4:17 am

Technical changes and errors reserved. It's up to the customer to check the suitability for a specific application by means of tests.