HellermannTyton

Technical data sheet

Article number:
151-04215 SENMT18M6

Material	Polyphenylene Sulfide (PPS), Steel (ST), Zinc plated (ZN)
Colour	Black (BK)

CE Certification	No
Fixation Method	Screw Mounting
Flammability	UL 94 HB
for Hole Ø (FH)	4.3 mm
Height (H)	47.5 mm
Length (L)	45.7 mm
Mounting Screw Type	#10 (M6) Screw
Operating Temperature	-40 °C to +150 °C
Package Content	1
Package Content packed in	pack
ROHS compliant	Yes
UV-Stabilised	No
Width (W)	38.0 mm

RoHS

created on 4. May 2026, 12:48 am

Technical changes and errors reserved. It´s up to the customer to check the suitability for a specific application by means of tests.