HellermannTyton

Technical data sheet

Article number:
151-04385 ROC18.5-22.5NXT

Product Group	Ratchet O-Clamp
Product Family	ROC Nextt Series
Material	Polyamide 6.6, high impact modified, heat and UV-stabilised (PA66HIRHSUV), Stainless Steel (SS)
Colour	Black (BK)

Bundle Ø max.	22.5 mm
Bundle Ø min.	18.5 mm
CE Certification	No
Fixation Method	Mounting Hanger
Flammability	UL 94 HB
Height (H)	83.7 mm
Length (L)	58.1 mm
Length (L2)	37.0 mm
Min.Tensile Strength	445 N
Operating Temperature	-40 °C to +105 °C
Package Content	200 pcs.
Package Content packed in	carton
ROHS compliant	Yes
UV-Stabilised	Yes
Width (W)	28.9 mm

HF ✓ RoHS ✓

created on 8. May 2026, 4:41 am

Technical changes and errors reserved. It´s up to the customer to check the suitability for a specific application by means of tests.