
Technical data sheet

Article number:
156-02226 **T50REC5A**



Product Group	2-piece fixing ties for edges
Product Family	EdgeClip-Series, 1.0 - 3.0 mm, side fixing
Material	Polyamide 6.6, high impact modified, heat and UV-stabilised, proprietary blend (PA66HIRHSUVR5), Polyamide 6.6, high impact modified, heat and UV-stabilised (PA66HIRHSUV)
Colour	Black (BK)

Application Tool	ProCut 9 no battery, MK3PNSP2, EVOcut, MK7P, MK10-SB, MK20, EVO7, EVO7SP, EVO7i, EVO7iSP, EVO9, EVO9SP, EVO9i, EVO9iSP
Bundle Ø max.	50.0 mm
Bundle Ø min.	5.0 mm
Cable Tie	Polyamide 6.6, high impact modified, heat and UV-stabilised (PA66HIRHSUV)
CE Certification	No
Fixation Method	Edge Clip
Flammability	UL 94 HB
Foot Part	Polyamide 6.6, high impact modified, heat and UV-stabilised, proprietary blend (PA66HIRHSUVR5)
Height (H)	15.5 mm
Length (L)	203.2 mm
Length (L2)	14.0 mm
Min.Tensile Strength	89 N
Operating Temperature	-40 °C to +115 °C, -40 °C to +110 °C
Package Content	100 pcs.
Package Content packed in	pack
Panel Thickness	1.0 - 3.0 mm
Panel Thickness max.	3.0 mm
Panel Thickness min.	1.0 mm
ROHS compliant	Yes
Thickness (T)	1.2 mm
UL-File Number	E64139
UV-Stabilised	Yes

created on 24. April 2026, 4:24 am

Variant	Inside Serrated
Width (W)	4.6 mm

RoHS

Technical changes and errors reserved. It´s up to the customer to check the suitability for a specific application by means of tests.