
Technical data sheet

Article number:
157-00306 **T50ROSFT6.5LG-E4**



Product Group	1-piece fixing ties with fir tree, with disc, for round holes
Product Family	Fir tree parts FT6
Material	Polyamide 6.6, high impact modified, heat and UV-stabilised (PA66HIRHSUV)
Colour	Black (BK)

Application Tool	MK3PNSP2, EVOcut, MK7P, MK10-SB, MK20, EVO7SP, EVO7i, EVO7iSP, FTS_pro
Bundle Ø max.	50.0 mm
Bundle Ø min.	2.0 mm
CE Certification	No
Fixation Method	Fir tree for round holes
Flammability	UL 94 V2
for Hole Ø (FH)	6.1 - 6.9 mm
Length (L)	218.44 mm
Min.Tensile Strength	225 N
Operating Temperature	-40 °C to +105 °C
Package Content	4000 pcs.
Package Content packed in	pack
Panel Thickness	0.6 - 8.25 mm
Panel Thickness max.	8.25 mm
Panel Thickness min.	0.6 mm
ROHS compliant	Yes
Thickness (T)	1.3 mm
UV-Stabilised	Yes
Width (W)	4.6 mm

RoHS

created on 22. May 2026, 12:14 pm

Technical changes and errors reserved. It´s up to the customer to check the suitability for a specific application by means of tests.