HellermannTyton

Technical data sheet

Article number:
156-04238 T50ROSX2SBS5-6U

Product Group	2-Piece Fixing Ties for Weld Studs
Material	Polyamide 6.6, heat stabilised (PA66HS), Polyamide 6.6, high impact modified, heat and UV-stabilised (PA66HIRHSUV)
Colour	Black (BK)

Bundle Ø max.	50.0 mm
Bundle Ø min.	4.0 mm
Cable Tie	Polyamide 6.6, heat stabilised (PA66HS)
CE Certification	No
Fixation Method	Stud Mount
Flammability	UL 94 HB
Height (H)	1.2 mm
Length (L)	202.0 mm
Min.Tensile Strength	200 N
Operating Temperature	-40 °C to +105 °C
Package Content	500 pcs.
Package Content packed in	pack
ROHS compliant	Yes
Stud Ø	5.0 mm, 6.0 mm
UV-Stabilised	Yes
Width (W)	4.6 mm

HF ✓ RoHS ✓

created on 22. May 2026, 12:30 pm

Technical changes and errors reserved. It's up to the customer to check the suitability for a specific application by means of tests.