HellermannTyton

Technical data sheet

Article number:
156-02245 T50SVCMOC12M

Product Group	2-piece fixing ties with pipe clip
Material	Polyamide 6.6, high impact modified, heat and UV-stabilised (PA66HIRHSUV)
Colour	Black (BK)

Bundle Ø max.	13.8 mm
Bundle Ø min.	10.5 mm
CE Certification	No
Fixation Method	Omega Clip
Flammability	UL 94 HB
Height (H)	34.1 mm
Length (L)	22.1 mm
Length (L2)	17.3 mm
Min.Tensile Strength	225 N
Operating Temperature	-40 °C to +105 °C
Package Content	1000 pcs.
Package Content packed in	pack
ROHS compliant	Yes
UV-Stabilised	Yes

HF RoHS

created on 24. April 2026, 4:25 am

Technical changes and errors reserved. It's up to the customer to check the suitability for a specific application by means of tests.