HellermannTyton

Technical data sheet

Article number:
151-03828 SLRCN12SM38

Material	Polyamide 6.6, high impact modified, heat and UV-stabilised (PA66HIRHSUV)
Colour	Black (BK)

Bundle Ø max.	38.1 mm
CE Certification	No
Fixation Method	Screw Mount
Flammability	UL 94 HB
for Hole Ø (FH)	M10 Threaded
Height (H)	72.0 mm
Length (L)	62.0 mm
Operating Temperature	-40 °C to +105 °C
Package Content	200 Carton
Package Content packed in	carton
ROHS compliant	Yes
Stud Size (Metric)	M10
Stud Ø	M5
UV-Stabilised	Yes
Width (W)	48.1 mm

HF RoHS

created on 24. July 2026, 2:26 pm

Technical changes and errors reserved. It's up to the customer to check the suitability for a specific application by means of tests.