HellermannTyton

Technical data sheet

Article number:
156-01429 T50RSB8SET

Material	Polyamide 6.6, heat stabilised (PA66HS), Polyamide 6.6, high impact modified, heat and UV-stabilised (PA66HIRHSUV)
Colour	Black (BK)
Application Tool	ProCut 9 no battery, MK3PNSP2, EVOcut, MK7P, MK10-SB, MK20, EVO7, EVO7SP, EVO7i, EVO7iSP, EVO9, EVO9SP, EVO9i, EVO9iSP
Bundle Ø max.	50.0 mm
Bundle Ø min.	4.0 mm
Cable Tie	Polyamide 6.6, heat stabilised (PA66HS)
CE Certification	No
Fixation Method	Stud Mount
Height (H)	25.0 mm
Length (L)	202.0 mm
Min.Tensile Strength	225 N
Operating Temperature	-40 °C to +105 °C
Package Content	2000 pc.
Package Content packed in	pack
ROHS compliant	Yes
Stud Ø	8.0 mm
Thickness (T)	1.2 mm
UV-Stabilised	Yes
Width (W)	4.6 mm

RoHS

created on 22. May 2026, 1:42 pm

Technical changes and errors reserved. It´s up to the customer to check the suitability for a specific application by means of tests.