HellermannTyton

Technical data sheet

Article number:
156-02652 IRCDFT9X17

Product Group	Heavy duty cable clamps
Product Family	screwable, Inline Ratchet Clamps
Material	Polyamide 6.6, high impact modified, heat and UV-stabilised (PA66HIRHSUV)
Colour	Black (BK)

Bundle Ø max.	50.8 mm
Bundle Ø min.	36.01 mm
CE Certification	No
Fixation Method	Fir Tree for oval holes
Flammability	UL 94 HB
for Hole Ø (FH)	9.0 x 17.0 mm
Length (L)	34.8 mm
Operating Temperature	-40 °C to +105 °C
Package Content	200 pcs.
Package Content packed in	pack
Panel Thickness	0.6 - 6.75 mm
Panel Thickness max.	6.75 mm
Panel Thickness min.	0.6 mm
ROHS compliant	Yes
UL-File Number	E64139
UV-Stabilised	Yes
Width (W)	34.9 mm

RoHS

c UL us

created on 22. May 2026, 9:18 am

Technical changes and errors reserved. It's up to the customer to check the suitability for a specific application by means of tests.