HellermannTyton

Technical data sheet

Article number:
151-03541 CMRCBLM8

Product Group	Heavy duty cable clamps
Product Family	screwable, Inline Ratchet Clamps
Material	Polyamide 6.6, high impact modified, heat and UV-stabilised (PA66HIRHSUV)
Colour	Black (BK)

Bundle Ø max.	19.56 mm
Bundle Ø min.	12.7 mm
CE Certification	No
Fixation Method	Screw Mount
Flammability	UL 94 HB
for Hole Ø (FH)	8.3 mm
Height (H)	30.4 mm
Length (L)	86.1 mm
Operating Temperature	-40 °C to +105 °C
Package Content	150 pcs.
Package Content packed in	pack
ROHS compliant	Yes
UL-File Number	E523406
UV-Stabilised	Yes
Width (W)	35.1 mm

HF RoHS

created on 4. September 2026, 9:47 am

Technical changes and errors reserved. It´s up to the customer to check the suitability for a specific application by means of tests.