
Technical data sheet

Article number:
157-00376 **T50SOSFT6.5-E4**



Product Group	1-piece fixing ties with fir tree, with disc, for round holes
Product Family	Fir tree parts FT6
Material	Polyamide 6.6, heat stabilised (PA66HS)
Colour	Black (BK)

Application Tool	ProCut 9 no battery, MK3PNSP2, EVOcut, MK7P, MK10-SB, MK20, EVO7, EVO7SP, EVO7i, EVO7iSP, EVO9, EVO9SP, EVO9i, EVO9iSP, FTS_pro
Bundle Ø max.	35.0 mm
Bundle Ø min.	1.0 mm
CE Certification	No
Fixation Method	Fir tree for round holes
Flammability	UL 94 HB
for Hole Ø (FH)	6.3 - 7.0 mm
Length (L)	161.5 mm
Min.Tensile Strength	225 N
Operating Temperature	-40 °C to +125 °C
Package Content	1000 pcs.
Package Content packed in	pack
Panel Thickness	0.6 - 4.2 mm
Panel Thickness max.	4.2 mm
Panel Thickness min.	0.6 mm
ROHS compliant	Yes
Thickness (T)	1.3 mm
UV-Stabilised	Yes
Width (W)	4.6 mm

RoHS

created on 26. June 2026, 2:33 pm

Technical changes and errors reserved. It´s up to the customer to check the suitability for a specific application by means of tests.