
Technical data sheet

Article number:
190-00128 SNP28



Product Group	Snapper hose clips for tubes and harnesses
Product Family	SNP-Series
Material	Polyamide 6.6, glass-fibre reinforced (PA66GF13)
Colour	Black (BK)

Application Tool	MSNP1-70, ASNP24-70
Bundle Ø max.	32.7 mm
Bundle Ø min.	28.5 mm
CE Certification	No
Fixation Method	Plug-in mounting
Flammability	UL 94 HB
Operating Temperature	-40 °C to +105 °C
Package Content	500 pcs.
Package Content packed in	pack
ROHS compliant	Yes
UV-Stabilised	No
Variant	Closed

RoHS

created on 10. July 2026, 2:09 pm

Technical changes and errors reserved. It's up to the customer to check the suitability for a specific application by means of tests.