
# Technical data sheet

## Article number:
## 190-00140 SNP32




| | |
|---|---|
| **Product Group** | Snapper hose clips for tubes and harnesses |
| **Product Family** | SNP-Series |
| **Material** | Polyamide 6.6, glass-fibre reinforced (PA66GF13) |
| **Colour** | Black (BK) |

| | |
|---|---|
| **Application Tool** | MSNP1-70, ASNP24-70 |
| **Bundle Ø max.** | 35.7 mm |
| **Bundle Ø min.** | 30.9 mm |
| **CE Certification** | No |
| **Fixation Method** | Plug-in mounting |
| **Flammability** | UL 94 HB |
| **Operating Temperature** | -40 °C to +105 °C |
| **Package Content** | 500 pcs. |
| **Package Content packed in** | pack |
| **ROHS compliant** | Yes |
| **UV-Stabilised** | No |
| **Variant** | Closed |

RoHS

created on 10. July 2026, 2:09 pm

Technical changes and errors reserved. It´s up to the customer to check the suitability for a specific application by means of tests.