
Technical data sheet

Article number:
190-00255 SNP12A



Product Group	Snapper hose clips for tubes and harnesses
Product Family	SNP-Series
Material	Polyamide 6.6, glass-fibre reinforced (PA66GF13)
Colour	Black (BK)

Bundle Ø max.	18.3 mm
Bundle Ø min.	15.6 mm
CE Certification	No
Fixation Method	Plug-in mounting
Flammability	UL 94 HB
Operating Temperature	-40 °C to +125 °C
Package Content	1000 pcs.
Package Content packed in	pack
ROHS compliant	Yes
UV-Stabilised	Yes
Variant	Closed

RoHS

created on 10. July 2026, 2:11 pm

Technical changes and errors reserved. It's up to the customer to check the suitability for a specific application by means of tests.