

18V Magnetic Light LXT®, DML819

1750 lx, 1200 lm

Model DML819 is a magnetic light powered by 18V LXT Li-ion battery.

This light can be used when performing maintenance work on construction machinery or heavy equipment, the light fixes with the magnet, allowing for hands free. It is easily attached in tight spaces. This work light is so compact and handy to hold with one hand. Features a foldable rotating LED head. Folds down to even more of a compact size.



Technical specifications

Nominal Battery Voltage	18 V
Voltage LXT	✓
Luminous flux	1200 / 800 / 500 Lumen
Illuminance	1750 / 1150 / 700 lx
Battery Chemistry (Ni-Cd / Ni-MH / Li-ion)	Li-ion
Color temperature	5000 K
Continuous Use 18V / 2.0 Ah Battery	3 / 4,5 / 7,5 h
Continuous Use 18V / 3.0 Ah Battery	4 / 6,5 / 10 h
Continuous Use 18V / 5.0 Ah Battery	7,5 / 11 / 18 h
Continuous Use 18V / 6.0 Ah Battery	9 / 14 / 22 h
Continuous Use 18V / 9.0 Ah Battery	14 / 22 / 35 h
Continuous Use 18V / 12.0 Ah Battery	18 / 29 / 46 h
Angle range horizontal	300 °
Angle range vertical	180 °
Product net weight	0,9 kg
Tool weight with battery	1,1 - 2,2 kg
Product Dimensions (L x W x H):	178 x 91 x 284 mm

User benefits

- Compact and lightweight for single handed operation
- Light diffusing lens softens LED light to reduce glare and provides widespread illumination
- 3 brightness settings (high / medium / low)
- eXtreme Protection Technology (XPT) is engineered for improved dust and water resistance for operation in harsh conditions
- Battery capacity warning function automatically notifies the user about reduction in battery capacity with the decrease of illuminance

EAN 0197050017536

Link to product - www.makitauk.com



Related products

Other

User manual

Parts drawing