10 ft DVI-D Single Link Cable - M/M

Product ID: DVIDSMM10



The DVIDSMM10DVI-D Single Link cable features 2 male DVI (19-pin) connectors and provides a reliable, purely digital connection between your desktop or laptop computer and a DVI-D monitor or projector.

The 10ft DVI-D male to male cable supports resolutions of up to 1920x1200 and transmission rates of up to 4.95 Gbits/sec, and is fully compliant with DVI DDWG standards.

Designed and constructed for maximum durability, this high quality digital video cable is backed by StarTech.com's Lifetime Warranty.

Certifications, Reports and Compatibility

Applications

• Connect your desktop or laptop computer to a DVI-D Single Link display or projector

Features

• Supports resolutions up to 1920x1200

• High-speed digital transmission rate of up to 4.95 Gbits/sec

• Aluminum-Mylar Foil with Braided Shielding

• Supports hot-plugging of DVI display devices

• Compliant with DVI DDWG Standards

General		
	UPC	065030795968
	Package Quantity	1
	Warranty	Lifetime
Physical & Environmental		
	Color	Black
	Wire Gauge	28 AWG
	Cable Length	10.0 ft [3.0 m]
	Product Length	10.0 ft [3.0 m]
	Product Width	0.0 in [0.0 mm]
	Product Height	0.0 in [0.0 mm]
	Weight of Product	10.9 oz [308.0 g]
Hardware		
	Connector Plating	Nickel
	Cable Jacket Material	PVC - Polyvinyl Chloride
	Cable Shield Material	Aluminum-Mylar Foil with Braid
	Industry Standards	DVI DDWG Standard
Packaging & In-the-Box		
	Included in Package	1 - 10 ft DVI-D Single Link Cable - M/M
	Package Width	7.0 in [17.7 cm]
	Package Depth	7.8 in [19.7 cm]
	Package Height	1.5 in [39 mm]
	Shipping (Package) Weight	10.9 oz [310 g]

Connector(s)		
	Connector 1 (Quantity)	1
	Connector 1	DVI-D Single-Link (19-Pin)
	Connector 2 (Quantity)	1
	Connector 2	DVI-D Single-Link (19-Pin)

Product appearance and specifications are subject to change without notice.