2m (6ft) High Speed HDMI Cable with Gripping Connectors, 4K 60Hz/1440p 144Hz, HDR10/HDCP 2.2/ARC, 18Gbps, UHD HDMI Cord for TV/Monitor/Display, TPE Jacket

Product ID: HDMI2-CABLE-GRIP-2M



This High Speed HDMI Cable is designed for reliable performance in enterprise, AV, and IT environments. HDMI 2.0 specifications are permanently etched into each connector-an exclusive feature that eliminates guesswork, ensures compatibility, and confirms the cable's ability to support high-bandwidth performance.

The HDMI UHD Cord features gold-plated gripping connectors to prevent accidental disconnections. The connectors attach securely to HDMI device ports, making this cable ideal for mounted and critical setups such as security systems and HDMI switches.

Drive sharp 4K video, fast refresh rates, and high-resolution visuals on UHD displays, workstations, video walls, and AV installations. This High Speed HDMI 2.0 cable supports 4K at 60Hz, 1440p at 144Hz, and 1080p at 240Hz at up to 18Gbps bandwidth for consistent, reliable signal quality.

Deliver deep contrast and accurate color with support for HDR10. Enable immersive multi-channel audio using ARC, Dolby Atmos, DTS:X, and 7.1 Dolby TrueHD. Maintain secure content delivery with HDCP 2.2 across HDMI 2.0 and legacy devices.

Route this HDMI cord easily around corners, behind displays, between desks and other equipment with a flexible, halogen-free TPE jacket rated to withstand over 2,000 bending cycles and robust connector strain reliefs. Aluminum-Mylar foil with braided shielding minimizes EMI in dense setups and shared spaces. Gold-plated connectors preserve signal integrity and resist corrosion, and are rated for 10,000+ insertions to support both daily wear and long-term use.

The terms HDMI, HDMI High-Definition Multimedia Interface, HDMI trade dress and the HDMI Logos are trademarks or registered trademarks of HDMI Licensing Administrator, Inc.

Certifications, Reports and Compatibility



Applications

Features

• Deliver High-Bandwidth 4K Video: 2m (6.6ft) HDMI 2.0 Cable delivers vivid, sharp 4K 60Hz UHD video with HDR10 and HDCP 2.2; Enable immersive sound quality with 32-channel audio, 7.1 surround, ARC, and DTS-HD Master Audio support

• Minimize Accidental Disconnections: Keep critical devices connected with latching HDMI connectors that resist unintentional unplugging due to vibration, tension, or handling; Ensure reliable signal transmission to mounted equipment with limited access

• Identify Specs Instantly: Etched HDMI 2.0 specs on each Quick ID connector remove guesswork and confirm feature support at-a-glance; The eco-friendly TPE jacket is flexible and durable, designed to withstand tight bends and is fully RoHS-compliant

• For High-Resolution Workflows: Achieve reliable 4K 60Hz performance with 18Gbps bandwidth in workstations and pro AV setups; Drive high refresh rates including 1440p 144Hz and 1080p 240Hz; Works w/USB-C to HDMI adapters for Apple M-series Pro/Max MacBooks

• The IT Pro's Choice: Our digital display cables are rigorously lab-tested for signal integrity, durability, and compatibility across HDMI, DisplayPort, USB-C, and legacy interfaces; Backed by free lifetime 24/5 multi-lingual technical assistance

General		
	UPC	065030925402
	Warranty	Lifetime
Physical & Environmental		
	Color	Black
	Material	Santoprene - Thermoplastic Rubber (TPE)
	Connector Style	Straight
	Wire Gauge	30 AWG
	Cable Length	6.6 ft [2 m]
	Cable OD	0.2 in [6 mm]

	Product Length	6.6 ft [2.0 m]
	Product Width	0.8 in [20.5 mm]
	Product Height	0.5 in [11.5 mm]
	Weight of Product	3.3 oz [93 g]
	Operating Temperature	0&degC to 40&degC (32&degF to 104&degF)
	Storage Temperature	-20&degC to 70&degC (-4&degF to 158&degF)
	Humidity	10% to 90%

Performance

	Maximum Data Transfer Rate	18Gbps
	Insertion Rating	Connectors rated beyond 10,000 insertions
	MTBF	Connectors rated beyond 10,000 insertions
	Audio Specifications	HDMI - 32 Channel Audio
	Maximum Digital Resolutions	4K 60Hz 1440p 144Hz 1080p 240Hz

Hardware

	Active or Passive Adapter	Passive
	Connector Plating	Gold
	Cable Jacket Material	TPE - Thermoplastic Elastomers
	Cable Shield Material	Aluminum-Mylar Foil with Braid
	Fire Rating	VW-1

Packaging & In-the-Box

	Included in Package	1 - HDMI 2.0 Cable
	Package Width	4.3 in [11 cm]
	Package Depth	7.5 in [19 cm]

	Package Height	0.9 in [23 mm]
	Shipping (Package) Weight	4.4 oz [125 g]

Connector(s)		
	Connector 1 (Quantity)	1
	Connector 1	HDMI
	Connector 2 (Quantity)	1
	Connector 2	HDMI

Product appearance and specifications are subject to change without notice.