3ft (91cm) High Speed HDMI Cable with Gripping Connectors, 4K 60Hz/1440p 144Hz, HDR10/HDCP 2.2/ARC, 18Gbps, UHD HDMI Cord for TV/Monitor/Display, TPE Jacket

Product ID: HDMI2-CABLE-GRIP-3F



Connect to a 4K UHD TV or monitor, using this High Speed HDMI&reg Cable. The connector markings enable quick visual identification, distinguishing this cable from other similar-looking or unmarked HDMI cables. Eliminate guesswork and always choose the appropriate cable to support full HDMI 2.0 capabilities.

The HDMI UHD Cord features gold-plated gripping connectors to prevent accidental disconnections. The connectors attach securely to HDMI device ports, making this cable ideal for critical A/V setups such as security systems and HDMI switches.

The HDMI Monitor Cable features a flexible TPE outer jacket that is tested to withstand 2,000 bending cycles at -/+60 degrees, and routes easily around corners and desk edges. Robust strain reliefs enable convenient positioning of the cable. The durable Gold-plated connectors are rated to operate beyond 10,000 insertions.

This High Speed HDMI&reg Cable supports full HDMI 2.0 features:

• Resolutions up to 4K 60Hz using a compatible HDMI source and display

• Supports high refresh rates including 1440p 144Hz and 1080p 240Hz

• 21:9 Aspect Ratio support for cinematic viewing experiences

• High Dynamic Range (HDR10) for higher contrast ratio and vibrant picture quality

• High-Bandwidth Digital Content Protection (HDCP) 2.2 for a secure connection between source and display

• Audio Return Channel (ARC) for sending audio from the TV back to an AV receiver or soundbar

• Up to 32 Uncompressed Digital Audio Channels

• HDMI Ethernet Channel (HEC) for network connectivity over HDMI

• Backward compatible with previous HDMI versions

This HDMI 2.0 Cable is constructed with braided aluminum mylar shielding to minimize EMI for clear, consistent audio/video output and long-term reliable performance.

The terms HDMI, HDMI High-Definition Multimedia Interface, HDMI trade dress and the HDMI Logos are trademarks or registered trademarks of HDMI Licensing Administrator, Inc.

Certifications, Reports and Compatibility

Applications

Features

• HIGH PERFORMANCE: High Speed HDMI Cable is designed for UHD-enabled HDMI devices; Choose the right HDMI cable at-a-glance with performance markings on connectors for quick and easy identification; Up to 18Gbps for seamless 4K 60Hz video

• GRIPPING HDMI CONNECTORS: This HDMI 2.0 cord features gold plated gripping male connectors to prevent accidental disconnection due to tension or vibration; Keeps cable securely connected to mounted HDMI displays and hard-to-access HDMI ports

• QUALITY CONSTRUCTION: Gold-plated connectors rated beyond 10,000 insertions; Durable TPE Jacket and strain reliefs are halogen-free and RoHS compliant; Tested to withstand 2,000 bending cycles at -/+60 degrees; Braided shield for enhanced EMI protection

• APPLICATIONS: Ideal for 4K UHD displays; Up to 144Hz refresh rate at 1440p resolution; Suitable for high performance GPUs and workstations; Connect an HDMI monitor to a 4K docking station

• SPECS: Black; 3-foot (0.9-meter); High Speed HDMI with Ethernet; HDMI 2.0 supports HDR10/ARC/HDCP 2.2/CEC; 4K 60Hz/1440p 144Hz/1080p 240Hz; 18Gbps; 32-ch Audio; Backward Compatible; 30AWG; 6mm (0.24in) O.D.

General		
	UPC	065030916370
	Warranty	Lifetime
Physical & Environmental		
	Color	Black

Material	Santoprene - Thermoplastic Rubber (TPE)
Connector Style	Straight
Wire Gauge	30 AWG
Cable Length	36.0 in [91.4 cm]
Cable OD	0.2 in [6 mm]
Product Length	36.7 in [93.3 cm]
Product Width	0.8 in [20.5 mm]
Product Height	0.5 in [11.5 mm]
Weight of Product	2.0 oz [56 g]
Operating Temperature	0&degC to 40&degC (32&degF to 104&degF)
Storage Temperature	-20&degC to 70&degC (-4&degF to 158&degF)
Humidity	10% to 90%

Performance

Maximum Data Transfer Rate	18Gbps
Insertion Rating	Connectors rated beyond 10,000 insertions
MTBF	Connectors rated beyond 10,000 insertions
Audio Specifications	HDMI - 32 Channel Audio
Maximum Digital Resolutions	4K 60Hz 1440p 144Hz 1080p 240Hz

Hardware

Active or Passive Adapter	Passive
Connector Plating	Gold
Cable Jacket Material	TPE - Thermoplastic Elastomers
Cable Shield Material	Aluminum-Mylar Foil with Braid

	Fire Rating	VW-1
Packaging & In-the-Box		
	Included in Package	1 - 3ft HDMI 2.0 Cable
	Package Width	5.0 in [12.8 cm]
	Package Depth	8.7 in [22 cm]
	Package Height	0.8 in [20 mm]
	Shipping (Package) Weight	2.2 oz [61 g]
Connector(s)		
	Connector 1 (Quantity)	1
	Connector 1	HDMI
	Connector 2 (Quantity)	1
	Connector 2	HDMI

Product appearance and specifications are subject to change without notice.