3m (10ft) USB4 Cable, 20Gbps, USB-IF Certified USB-C Cable, 60W PD, 4K 120Hz DP 2.1, TPE Jacket, Black USB-C Cord

Product ID: CC3M20GUSB4CX



Connect reliably to USB Type-C (USB4) devices, delivering up to 20Gbps, 4K 120Hz video, and 60W of Power Delivery. Each connector is laser-etched with USB4 specifications, an exclusive feature that eliminates guesswork, confirms compatibility, and verifies USB4 performance.

Safely power USB-C laptops and devices with up to 60W of Power Delivery using a compatible USB-C docking station or wall charger. An integrated E-marker chip ensures accurate power negotiation for stable, consistent charging. Ideal for portable laptops such as Apple M-series Air/Pro MacBooks

Enable full-speed, spec-compliant USB4 performance with a USB-IF Certified cable designed for demanding power, data, and display applications. Rigorously tested to meet electrical and mechanical standards, it ensures reliable interoperability, signal integrity, and consistent operation across a wide range of USB-C devices. The USB4 cable features shielded 28/34AWG coaxial wire for optimal EMI protection.

Drive sharp 4K 120Hz video or dual 4K 60Hz displays via DisplayPort 2.1 Alt Mode with DSC, HBR3, and HDR10 support. Suitable for professional 3D rendering, high-frame-rate video, and bandwidth-intensive visual workflows. This USB4 cable integrates seamlessly with USB-C docks, and maintains backward compatibility with a wide range of resolutions and refresh rates.

The USB4 Cable features a TPE outer jacket for optimal flexibility and wear protection. The durable nickel-plated connectors are designed for frequent daily use, and are rated to operate beyond 10,000 insertion cycles. The 3-meter (10-foot) cable length is ideal for larger desk workstations where extra reach is desired.

Certifications, Reports and Compatibility

Applications

• Designed for seamless operation with USB-C docking stations and external devices

• Drive sharp 4K 120Hz video or support dual 4K 60Hz UHD displays

• Transfer data at 20 Gbps speeds and 60W of power over a USB4 connection

• Power and charge USB4/USB-C, and Thunderbolt devices

Features

• Versatile USB4 Performance: Enhance productivity with USB4 capabilities, featuring 4K 120Hz video, 20Gbps, and 60W charging over a single connection; The 3-meter (10-foot) cable length is ideal for larger workspaces where extra reach is desired

• Safe, Certified Compatibility: Trust this USB-IF Certified Cable to ensure peak USB4 performance in critical workflows, with E-marker chip for safe and consistent Power Delivery to USB-C devices; Certified cables guarantee full USB4 and backward compatibility

• Identify Specs Instantly: Swiftly identify this USB4 cable with Quick ID connector markings; Durable TPE jacket is rugged and flexible, and is designed to withstand tight bends; Shielded 28/34AWG coaxial wire minimizes EMI

• Ultra-Fast Docking Cable: Designed to work seamlessly with USB-C docking stations; Drive a 4K 120Hz or dual 4K 60Hz displays via DP2.1 w/DSC for professional 3D imaging; Ideal for high-performance laptops such as Apple M-series Air/Pro MacBooks

• The IT Pro's Choice: Our USB-C cables are rigorously tested in our in-house Innovation Lab for reliable performance, durable construction, and broad compatibility with a variety of devices; Backed by free lifetime 24/5 multi-lingual technical assistance

General		
	UPC	065030922685
	Warranty	Lifetime
Power		
	Power Delivery	60W
	Input Current	3A
Physical & Environmental		
	Color	Black
	Material	TPE

Connector Style	Straight
Wire Gauge	28/34 AWG
Cable Length	10.0 ft [3.0 m]
Cable OD	0.2 in [5.5 mm]
Product Length	9.9 ft [3.0 m]
Product Width	0.5 in [12.8 mm]
Product Height	0.3 in [6.9 mm]
Weight of Product	5.9 oz [168 g]
Operating Temperature	0&degC to 60&degC (32&degF to 140&degF)
Storage Temperature	-20C to 60C (-4F to 140F)
Humidity	40 - 65% RH

Performance

HDR Support	HDR10
Maximum Data Transfer Rate	20 Gbps
Type and Rate	USB4 (20Gbps)
Supported Protocols	USB4 USB 3.2 DisplayPort 2.1 Alt Mode Power Delivery 3.0 ,
Audio Specifications	DisplayPort - 32 Channel Audio
Maximum Digital Resolutions	4K 120Hz
Video Revision	DisplayPort 2.1

Hardware

Active or Passive Adapter	Passive
Connector Plating	Nickel
Cable Jacket Material	TPE - Thermoplastic Elastomers

	Cable Shield Material	Aluminum-Mylar Foil with Braid
Packaging & In-the-Box		
	Included in Package	1 - USB4 Cable - 20Gbps
	Package Width	3.1 in [80 mm]
	Package Depth	9.1 in [23 cm]
	Package Height	1.2 in [30 mm]
	Shipping (Package) Weight	6.7 oz [191 g]
Connector(s)		
	Connector 1 (Quantity)	1
	Connector 1	USB-C (20Gbps, 65W)
	Connector 2 (Quantity)	1
	Connector 2	USB-C (20Gbps, 65W)

Product appearance and specifications are subject to change without notice.