10 ft Micro USB Cable - A to Micro B

Product ID: UUSBHAUB10

The UUSBHAUB10 10-foot USB A to Micro USB cable features one USB ‘A’ male connector, and one ‘Micro-B’ male connector, providing a high quality connection to USB 2.0 mobile devices (such as BlackBerry or Android-based cellular phones, digital cameras, PDA’s, Tablet PC devices and GPS systems) that use a Micro USB connector to a USB capable computer for everyday tasks such as data synchronization and file transfers.

This high quality cable is backed by StarTech.com's Lifetime Warranty to ensure dependable, long-lasting connections between Micro USB and USB devices.

Certifications, Reports and Compatibility

Applications

• An ideal replacement cable for connecting mobile devices to a USB capable computer

Features

• Supports high speed data transfer rates up to 480 Mbps

• Aluminum-Mylar Foil with Braided Shielding

• High quality USB 'A' and USB 'Micro-B’connectors

• Durable PVC construction

General		
	UPC	065030828154
	Package Quantity	1
	Warranty	Lifetime
Physical & Environmental		
	Color	Black
	Wire Gauge	24/30 AWG
	Cable Length	10.0 ft [3.0 m]
	Product Length	10.0 ft [3.1 m]
	Product Width	0.6 in [16.0 mm]
	Product Height	0.3 in [7.0 mm]
	Weight of Product	2.4 oz [68.0 g]
	Operating Temperature	-20C to 60C (-4F to 140F)
	Storage Temperature	-10C to 30C (14F to 86F)
	Humidity	30%-75% RH
Performance		
	Type and Rate	USB 2.0 (480Mbps)
Hardware		
	Connector Plating	Nickel
	Cable Jacket Material	PVC - Polyvinyl Chloride
	Cable Shield Material	Aluminum-Mylar Foil with Braid
Packaging & In-the-Box		
	Included in Package	1 - 10 ft Micro USB Cable - A to Micro B
	Package Width	5.8 in [14.8 cm]
	Package Depth	5.0 in [12.6 cm]

	Package Height	0.7 in [19 mm]
	Shipping (Package) Weight	2.8 oz [78 g]

Connector(s)		
	Connector 1 (Quantity)	1
	Connector 1	USB-A (480Mbps, 2.5W)
	Connector 2 (Quantity)	1
	Connector 2	USB Micro-B (480Mbps, 2.5W)

Product appearance and specifications are subject to change without notice.